

Part No: 4731L3-007SR

Valves

3-Way Ball Valve

Desc: 3/4 PVC T/U IND 3WAY VERT L/3 SR/THD FKM

MSRP: 395.79

Part Code: 615

Weight(lbs): 0.827

Weight(kg): 0.375

Weight(gm): 375

Size: 3/4"

Color: GRAY

Material: PVC



G = 2

A = 2- 1/4

B = 2- 3/4

C = 4- 1/4

D = 2- 7/8

E = 3- 5/16

F = 2- 3/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

