

Part No: 4732L1-030C

Valves

3-Way Ball Valve

Desc: 3 CPVC T/U IND 3WAY VERT L/I SOC FKM

MSRP: 2335.26

Part Code: 617

Weight(lbs): 10.179

Weight(kg): 4.617

Weight(gm): 4617

Size: 3"

Color: GRAY

Material: CPVC



Type Single L - Port (Vertical)
Connection Socket
O-Ring FKM

A = 6-3/16

B = 7

C = 10-3/4

D = 5-7/8

E = 7-5/8

F = 6-3/4

G = 4-7/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

