

**Part No:** 4732L2-005C

**Valves**

**3-Way Ball Valve**

**Desc:** 1/2 CPVC T/U IND 3WAY VERT L/2 SOC FKM

**MSRP:** 546.92

**Part Code:** 617

**Weight(lbs):** 0.538

**Weight(kg):** 0.244

**Weight(gm):** 244

**Size:** 1/2"

**Color:** GRAY

**Material:** CPVC



**A** = 1-15/16

**B** = 2-1/2

**C** = 4-1/4

**D** = 2-17/32

**E** = 2-7/8

**F** = 2-11/16

**G** = 1-13/16

**Type** Double L - Port (Vertical)  
**Connection** Socket  
**O-Ring** FKM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

