

Part No: 4732T1-015C

Valves

3-Way Ball Valve

Desc: 1-1/2 CPVC T/U IND 3WAY VRT T/PT SOC FKM

MSRP: 576.3

Part Code: 617

Weight(lbs): 2.344

Weight(kg): 1.063

Weight(gm): 1063

Size: 1-1/2"

Color: GRAY

Material: CPVC



Type T - Port (Vertical)
Connection Socket
O-Ring FKM

A = 3- 1/2 B = 3- 1/2 C = 6- 1/4 D = 4 E = 4- 3/16
 F = 4- 3/16 G = 2- 9/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

