

Part No: 4732T1-025

Valves

3-Way Ball Valve

Desc: 2-1/2 PVC T/U IND 3WAY VERT T/PT SOC FKM

MSRP: 1491.01

Part Code: 615

Weight(lbs): 9.392


Weight(kg): 4.26

Weight(gm): 4260

Size: 2-1/2"

Color: GRAY

Material: PVC



A = 5- 3/8

B = 5- 7/8

C = 9- 5/16

D = 5- 1/8

E = 6- 1/4

F = 5- 7/8

G = 4- 3/8

Type T - Port (Vertical)

Connection Socket

O-Ring FKM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

