

Part No: 4734L3-007C

All

INTL-1

Desc: 25MM CPVC TUK2 VRT 3WAY BV L3/PT FKM DIN

MSRP: 598.42

Part Code: 239

Weight(lbs): 0.851

Weight(kg): 0.386

Weight(gm): 386

Size: 25MM

Color:

Material:

Connection DIN SOC with L3 Port

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

