

**Part No:** 4737T1-025C

**Valves**

**3-Way Ball Valve**

**Desc:** 2-1/2 CPVC T/U IND 3WAY VRT T/PT SPG FKM

**MSRP:** 2293.91

**Part Code:** 617

**Weight(lbs):** 10.212

**Weight(kg):** 4.632

**Weight(gm):** 4632

**Size:** 2-1/2

**Color:** GRAY

**Material:** CPVC



**A** = 5- 3/8

**B** = 5- 7/8

**C** = 11- 3/8

**D** = 5- 1/8

**E** = 6- 1/4

**F** = 6- 7/16

**G** = 4- 3/8

**Type** T - Port (Vertical)

**Connection** Spigot

**O-Ring** FKM

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

