

Part No: 4737T1-030

Valves

3-Way Ball Valve

Desc: 3 PVC T/U IND 3WAY VERT T/PT SPG FKM

MSRP: 1518.03

Part Code: 615

Weight(lbs): 9.817

Weight(kg): 4.453

Weight(gm): 4453

Size: 3

Color: GRAY

Material: PVC



A = 6-3/16

B = 6-7/8

C = 11-9/16

D = 5-7/8

E = 7-5/8

F = 7-3/16

G = 4-7/8

Type T - Port (Vertical)

Connection Spigot

O-Ring FKM

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

