

Part No: 476-666F

Fabricated Fittings

Double Wye

Desc: 12X6 PVC RED DBL WYE SOC 100PSI SCH40 G

MSRP: 2277.11

Part Code: 047

Weight(lbs): 42.593


Weight(kg): 19.32

Weight(gm): 19320

Size: 12"X6"

Color: WHITE

Material: PVC



Schedule SCH 40

Connection Socket X Socket X Socket X
Socket


Type Reduction

G = 2- 3/8 **G1** = 15- 5/8 **G2** = 15- 1/8 **H** = 8- 5/8 **H1** = 18- 7/8
H2 = 21- 3/8 **L** = 30 **M** = 13- 9/16 **M1** = 7- 3/16

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.
- L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; ± 1/4 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.
- W** = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006