

Part No: 478-012

Schedule 40 White

Adapter

Desc: 1-1/4 PVC SPG FEMALE ADAPT SPGXFPT SCH40

MSRP: 3.56

Part Code: 040

Weight(lbs): 0.137

Weight(kg): 0.062

Weight(gm): 62


Size: 1-1/4"

Color: WHITE

Material: PVC

Connection Spigot x Fipt

Type Standard



L = 2-9/16

M1 = 2-3/32

N = 3/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

