

Part No: 5032L1-015C

Valves

3-Way Ball Valve

Desc: 1-1/2 CPVC T/U IND 3WY L/1 HOR SOC FKM

MSRP: 568.41

Part Code: 617

Weight(lbs): 2.339

Weight(kg): 1.061

Weight(gm): 1061

Size: 1-1/2"


Color: GRAY

Material: CPVC

Type L - Port (Horizontal)

Connection Socket

O-Ring FKM



A = 3-5/8

B = 3-5/8

C = 6-3/8

D = 4

E = 4- 3/16

F = 4-5/16

G = 2-15/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

