

Part No: 5037L1-020

Valves

3-Way Ball Valve

Desc: 2 PVC T/U IND 3WAY L/1 HOR SPG FKM

MSRP: 482.67

Part Code: 615

Weight(lbs): 3.957

Weight(kg): 1.795

Weight(gm): 1795

Size: 2


Color: GRAY

Material: PVC

Type L - Port (Horizontal)

Connection Spigot

O-Ring FKM



G = 3-3/4

A = 4- 1/4

B = 4- 3/4

C = 8-1/4

D = 4- 1/2

E = 8-1/4

F = 5-5/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

