

Part No: 5038L1-007C

All

INTL-1

Desc: 20MM CPVC TU2K HOR 3WAY BV L1/PT FKM JIS

MSRP: 340.08

Part Code: 239

Weight(lbs): 0.831

Weight(kg): 0.377

Weight(gm): 377

Size: 20MM

Color:

Material:

Connection JIS SOC with L1 Port

Under

Development

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

