

Part No: 5810-01008

Swing Joints

Riser Assemblies

Desc: 1 PVC SWING JOINT RISER W/8 NIP SPGXMAT

MSRP: 87

Part Code: 030

Weight(lbs): 1.561


Weight(kg): 0.708

Weight(gm): 708

Size: 1"

Color: BLUE

Material: PVC



Inlet Spigot

Outlet MAT

Riser Type Buttress Thread

Type Standard

Riser Nipple Length 8

A = 8

B = 9- 9/16

C = 12- 7/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

