

Part No: 5811-01010

Swing Joints

Riser Assemblies

Desc: 1 PVC SWING JOINT RISER W/10 NIP MPTXMAT

MSRP: 91.66

Part Code: 030

Weight(lbs): 1.662

Weight(kg): 0.754

Weight(gm): 754

Size: 1"

Color: BLUE

Material: PVC

Inlet Mipt

Outlet MAT

Riser Type Buttress Thread

Type Standard

Riser Nipple Length 10

A = 10

B = 11- 9/16

C = 14- 7/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

