

Part No: 591-010-6A

Swing Joints

Riser Assemblies

Desc: 1 PVC 90 ELL SWING JOINT FBT SCH80

MSRP: 30.66

Part Code: 030

Weight(lbs): 0.408

Weight(kg): 0.185

Weight(gm): 185

Size: 1"

Color: BLUE

Material: PVC

Under

Development

A = 1-23/73

A1 = 1-23/73

C = 1-11/16

C1 = 1-11/16

D = 1- 3/25

M = 1-31/32

M1 = 1-31/32

G = 13/16

G1 = 13/16

H = 2- 1/2

H1 = 2- 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

