

Part No: 593-249-5A

Swing Joints

Riser Assemblies

Desc: 2X1 PVC SWING JOINT RED TEE SOCXFBT D

MSRP: 54.42

Part Code: 030

Weight(lbs): 0.794

Weight(kg): 0.36

Weight(gm): 360

Size: 2"X1"

Color: BLUE

Material: PVC

Under

Development

A = 2- 3/8	A1 = 1-23/73	A2 = 2- 3/8	C = 1-31/32	C1 = 1-11/16
C2 = 1-31/32	M2 = 2-23/32	N = 2- 9/32	H = 2-31/32	H1 = 3- 1/8
H2 = 2-31/32	L = 5-15/16	M = 2- 7/8	M1 = 1-31/32	D = 2- 9/29
D1 = 1- 3/25	D2 = 2- 9/29	G = 1	G1 = 1- 7/16	G2 = 1

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References