

Part No: 6623-005C

Valves

Compact Ball Valve

Desc: 1/2 CPVC COMPACT 2000 BALLVALVE FLG EPDM

MSRP: 114.57

Part Code: 212

Weight(lbs): 0.62


Weight(kg): 0.281

Weight(gm): 281

Size:

Color: GRAY

Material: CPVC



Type Compact 2000
Connection Flanged
O-Ring EPDM
Pressure Rating 150 psi @ 73° F

A = 1- 7/16

B = 1- 5/8

C = 3- 1/16

D = 1- 5/8

E = 2- 1/2

F = 3-1/2

G = 2-11/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

