

Part No: 7121L1-015SR

Valves

3-Way Full Port Ball Valve

Desc: 1-1/2 PVC TU IND 3WFP VRT L1 SRFPT EPDM

MSRP: 392.88

Part Code: 615

Weight(lbs): 3.77

Weight(kg): 1.71

Weight(gm): 1710

Size: 1-1/2

Color: GRAY

Material: PVC



A = 4

B = 6-1/4

C = 8-1/8

D = 4-3/16

E = 4-3/16

F = 4-1/16

G = 3-1/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

