

Part No: 7121T1-012CSR

Valves

3-Way Full Port Ball Valve

Desc: 1-1/4 CPVC TU IND 3WFP VRT T1 SRFPT EPDM

MSRP: 475.66

Part Code: 617

Weight(lbs): 2.895

Weight(kg): 1.313

Weight(gm): 1313

Size: 1-1/4

Color: GRAY

Material: CPVC



A = 3-9/16

B = 5-5/8

C = 7-5/8

D = 3-3/4

E = 3-7/8

F = 3-3/4

G = 2-13/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

