

Part No: 7122L1-020C

Valves

3-Way Full Port Ball Valve

Desc: 2 CPVC TU IND 3WFP VRT L1 SOC EPDM

MSRP: 645

Part Code: 617

Weight(lbs): 5.728


Weight(kg): 2.598

Weight(gm): 2598

Size: 2

Color: GRAY

Material: CPVC



A = 4-5/8

B = 7-5/16

C = 10-11/32

D = 4-9/16

E = 5-3/32

F = 5-1/4

G = 3-23/32

Type Single L - Port (Vertical)
Connection Socket
O-Ring EPDM
Pressure Rating 235 psi @ 73° F

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

