

**Part No:** 7131L3-015SR

**Valves**

**3-Way Full Port Ball Valve**

**Desc:** 1-1/2 PVC TU IND 3WFP VRT L3 SRFPT FKM

**MSRP:** 566.41

**Part Code:** 615

**Weight(lbs):** 3.805

**Weight(kg):** 1.726

**Weight(gm):** 1726

**Size:** 1-1/2

**Color:** GRAY

**Material:** PVC



**F** = 4-1/16

**G** = 3-1/8

**A** = 4

**B** = 6-1/4

**C** = 8-1/8

**D** = 4-3/16

**E** = 4-3/16

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

