

Part No: 7131T1-005SR

Valves

3-Way Full Port Ball Valve

Desc: 1/2 PVC TU IND 3WFP VRT T1 SRFPT FKM

MSRP: 215.76

Part Code: 615

Weight(lbs): 0.774


Weight(kg): 0.351

Weight(gm): 351

Size: 1/2

Color: GRAY

Material: PVC



F = 2-1/2

G = 1-13/16

A = 2-1/8

B = 3-5/8

C = 5

D = 2-5/8

E = 2-13/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

