

Part No: 7132L3-005

Valves

3-Way Full Port Ball Valve

Desc: 1/2 PVC TU IND 3WFP VRT L3 SOC FKM

MSRP: 257.14

Part Code: 615

Weight(lbs): 0.756

Weight(kg): 0.343

Weight(gm): 343

Size: 1/2

Color: GRAY

Material: PVC



E = 2-13/16

F = 2-11/16

G = 1-13/16

A = 2-1/8

B = 3-5/8

C = 5-3/8

D = 2-5/8

Type Triple L - Port (Vertical)
Connection Socket
O-Ring FKM
Pressure Rating 235 psi @ 73° F

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

