

Part No: 721311L-030C

Valves

Butterfly Valve

Desc: 3 CPVC TL BFV BUNA W/HANDLE SS/LUG

MSRP: 1744.87

Part Code: 252

Weight(lbs): 7.923

Weight(kg): 3.594

Weight(gm): 3594

Size: 3"


Color: GRAY

Material: CPVC

Design True Lug (SS)

Handle Lever Handle

O-Ring Buna-N



A = 11- 1/2

B = 2-13/16

C = 7- 1/2

D = 7-27/32

E = 12

F = 5- 5/8

**No of
Bolts** = 4

**Bolt
Circle
Dia.** = 6

Bolt Size = 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

