

Part No: 721311L-040C

Valves

Butterfly Valve

Desc: 4 CPVC TL BFV BUNA W/HANDLE SS/LUG

MSRP: 3120.09

Part Code: 252

Weight(lbs): 11.55

Weight(kg): 5.239

Weight(gm): 5239

Size: 4"


Color: GRAY

Material: CPVC

Design True Lug (SS)

Handle Lever Handle

O-Ring Buna-N



A = 13

B = 3

C = 9

D = 8- 1/2

E = 12

F = 6- 1/4

No of Bolts = 8

Bolt Circle Dia. = 7- 1/2

Bolt Size = 1/2

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

