

Part No: 721311L-060C

Valves

Butterfly Valve

Desc: 6 CPVC TL BFV BUNA W/HANDLE SS/LUG

MSRP: 4075.56

Part Code: 252

Weight(lbs): 19.079

Weight(kg): 8.654

Weight(gm): 8654

Size: 6"


Color: GRAY

Material: CPVC

Design True Lug (SS)

Handle Lever Handle

O-Ring Buna-N



A = 16-13/32

B = 3-13/32

C = 11- 1/16

No of Bolts = 8

Bolt Circle Dia. = 9- 1/2

Bolt Size = 5/8

D = 10- 7/8

E = 13-15/16

F = 8- 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

