

**Part No:** 721311Z-080

**Valves**

**Butterfly Valve**

**Desc:** 8 PVC TL BFV BUNA W/HANDLE ZINC/LUG

**MSRP:** 3365.51

**Part Code:** 250

**Weight(lbs):** 23.647

**Weight(kg):** 10.726

**Weight(gm):** 10726

**Size:** 8"

**Color:** GRAY

**Material:** PVC

**Design** True Lug (Zinc)

**Handle** Lever Handle

**O-Ring** Buna-N



**A** = 18- 5/8

**B** = 3-23/32

**C** = 13- 1/2

**D** = 12

**E** = 13-15/16

**F** = 9- 1/2

**No of Bolts** = 8

**Bolt Circle Dia.** = 11- 3/4

**Bolt Size** = 5/8

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

