

**Part No:** 722301L-100

**Valves**

**Butterfly Valve**

**Desc:** 10 PVC TL BFV EPDM L/GOP WITH S/S LUG

**MSRP:** 7928.41

**Part Code:** 250

**Weight(lbs):** 39.145

**Weight(kg):** 17.756

**Weight(gm):** 17756

**Size:** 10"

**Color:** GRAY

**Material:** PVC

**Design** True Lug (SS)

**Handle** Valve Only

**O-Ring** EPDM



**B** = 4- 1/4

**C** = 16

**F** = 11

**No of Bolts** = 12

**Bolt Circle Dia.** = 14- 1/4

**Bolt Size** = 3/4

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Molded Dimension References

