

Part No: 722301L-100C

Valves

Butterfly Valve

Desc: 10 CPVC TL BFV EPDM L/GOP WITH S/S LUG

MSRP: 9971.44

Part Code: 252

Weight(lbs): 39.641

Weight(kg): 17.981

Weight(gm): 17981

Size: 10"

Color: GRAY

Material: CPVC

Design True Lug (SS)

Handle Valve Only

O-Ring EPDM



B = 4- 1/4

C = 16

F = 11

No of Bolts = 12

Bolt Circle Dia. = 14- 1/4

Bolt Size = 3/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

