

Part No: 801-040BL

Low Extractable

Tee

Desc: 4 PVC LE TEE SOC SCH80

MSRP: 394.56

Part Code: 065

Weight(lbs): 3.433

Weight(kg): 1.557

Weight(gm): 1557


Size: 4"

Color: BLUE

Material: PVC LE

Connection Socket x Socket x Socket

Type Tee



M = 5- 1/4

G = 2- 5/8

H = 4- 7/8

L = 9- 3/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

