

Part No: 802-005CBR

Schedule 80 PVC & CPVC

Tee

Desc: 1/2 CPVC TEE SOCXBRFPT SCH80

MSRP: 98.02

Part Code: 096

Weight(lbs): 0.165

Weight(kg): 0.075

Weight(gm): 75


Size: 1/2"

Color: GRAY

Material: CPVC

Connection Socket x Socket x Brass Fipt

Type Standard



L = 2- 5/8

M = 1- 5/32

M1 = 1- 7/32

G = 7/8

G1 = 31/32

H = 1- 7/16

H1 = 1-17/32

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

