

Part No: 806-020BL

Low Extractable

Elbow

Desc: 2 PVC LE 90 ELL SOC SCH80

MSRP: 71.58

Part Code: 065

Weight(lbs): 0.606

Weight(kg): 0.275

Weight(gm): 275


Size: 2"

Color: BLUE

Material: PVC LE

Connection Socket x Socket

Type 90° Elbow



G = 1- 7/16

H = 2-15/16

M = 2- 7/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

