

Part No: 817-030BL

Low Extractable

Elbow

Desc: 3 PVC LE 45 ELL SOC SCH80

MSRP: 227.6

Part Code: 065

Weight(lbs): 1.131

Weight(kg): 0.513

Weight(gm): 513


Size: 3"

Color: BLUE

Material: PVC LE

Connection Socket x Socket

Type 45° Elbow



H = 2-27/32

J = 31/32

M = 4- 1/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

