

Part No: 817-050F

Fabricated Fittings

Elbow

Desc: 5 PVC 45 ELL SOC SCH80

MSRP: 203.3

Part Code: 083

Weight(lbs): 3.748

Weight(kg): 1.7

Weight(gm): 1700

Size: 5"

Color: GRAY


Material: PVC

Schedule SCH 80

Angle 45 Degree

Connection Socket X Socket

Type Standard



H = 4- 7/8

J = 1- 7/8

M = 6- 5/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

