

Part No: 817-200CF

Fabricated Fittings

Elbow

Desc: 20 CPVC 45 ELL SOC SCH80

MSRP: 14977.88

Part Code: 097

Weight(lbs): 124.773


Weight(kg): 56.596

Weight(gm): 56596

Size: 20"

Color: GRAY

Material: CPVC



H = 16- 3/4

J = 6- 3/4

M = 22- 1/16

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

L = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; ± 1/4 inch.

N = Socket bottom to socket bottom; couplings; ± 1/2 inch.

W = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

