

Part No: 8170V-002C

Schedule 80 PVC & CPVC

Tank Adapter

Desc: 1/4 CPVC TANK ADAPTER SOCXSOC FKM GASKET

MSRP: 121.03

Part Code: 101

Weight(lbs): 0.117

Weight(kg): 0.053

Weight(gm): 53


Size: 1/4"

Color: GRAY

Material: CPVC

Connection Socket x Socket (New Style)

Gasket FKM



L = 2-15/32

L1 = 1-13/16

M = 1-17/32

M1 = 1-1/32

N = 1- 3/16

R = 1/2

Min Hole Size = 1-1/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

