

Part No: 8171V-003SR

Schedule 80 PVC & CPVC

Tank Adapter

Desc: 3/8 PVC TANK ADAPT SOCXSRFPT FKM GASKET

MSRP: 100.42

Part Code: 100

Weight(lbs): 0.134

Weight(kg): 0.061

Weight(gm): 61


Size: 3/8"

Color: GRAY

Material: PVC

Connection Socket x SR Fipt (New Style)

Gasket FKM



L = 2-17/32

L1 = 1-27/32

M = 1-21/32

M1 = 1-5/32

N = 1- 3/16

R = 1/2

Min Hole Size = 1-3/16

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

