

**Part No:** 8172V-025C

**Schedule 80 PVC & CPVC**

**Tank Adapter**

**Desc:** 2-1/2 CPVC TANK ADAPT FPTXFPT FKM GASKET

**MSRP:** 634.4

**Part Code:** 101

**Weight(lbs):** 2.222

**Weight(kg):** 1.008

**Weight(gm):** 1008


**Size:** 2-1/2"

**Color:** GRAY

**Material:** CPVC

**Connection** Fipt x Fipt (New Style)

**Gasket** FKM



**L** = 4-17/32

**L1** = 3-19/32

**M** = 5- 1/4

**M1** = 3-13/16

**N** = 2-7/32

**R** = 1

**Min Hole  
Size** = 3-7/8

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

