

## Metric Fittings & Valves PVC Transition Unions



Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
-------------	------	--------	----------	-----------	------------

### PVC Transition Union

**DIN (mm) Soc x ASTM (in.) Soc with Viton® O-ring Seal**



235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8657-020	<b>20 d X 1/2</b>	10	60	197	10.46
8657-025	<b>25 d X 3/4</b>	10	40	197	13.32
8657-032	<b>32 d X 1</b>	10	40	197	15.20
8657-040	<b>40 d X 1-1/4</b>	10	0	197	30.19
8657-050	<b>50 d X 1-1/2</b>	10	0	197	34.19
8657-063	<b>63 d X 2</b>	5	0	197	46.37
8657-090	<b>90 d X 3</b>	5	0	197	86.31
8657-110	<b>110 d X 4</b>	4	0	197	120.21

### PVC Transition Union

**DIN (mm) Soc x ASTM (in.) Fipt with Viton® O-ring Seal**



235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8658-020	<b>20 d X 1/2</b>	10	60	197	12.78
8658-025	<b>25 d X 3/4</b>	20	80	197	17.86
8658-032	<b>32 d X 1</b>	15	90	197	23.76
8658-040	<b>40 d X 1-1/4</b>	10	0	197	45.37
8658-050	<b>50 d X 1-1/2</b>	10	0	197	56.16
8658-063	<b>63 d X 2</b>	5	0	197	86.41
8658-090	<b>90 d X 3</b>	5	0	197	203.98
8658-110	<b>110 d X 4</b>	4	0	197	234.43

### PVC Transition Union

**DIN (mm) Soc x ASTM (in.) Soc with EPDM O-ring Seal**



235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8697-020	<b>20 d X 1/2</b>	20	240	197	10.33
8697-025	<b>25 d X 3/4</b>	10	60	197	13.16
8697-032	<b>32 d X 1</b>	15	90	197	15.05
8697-040	<b>40 d X 1-1/4</b>	10	0	197	29.83
8697-050	<b>50 d X 1-1/2</b>	10	0	197	33.77
8697-063	<b>63 d X 2</b>	5	0	197	45.80
8697-090	<b>90 d X 3</b>	5	0	197	85.23
8697-110	<b>110 d X 4</b>	4	0	197	117.88

### PVC Transition Union

**DIN (mm) Soc x ASTM (in.) Fipt with EPDM O-ring Seal**



235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8698-020	<b>20 d X 1/2</b>	20	160	197	12.60
8698-025	<b>25 d X 3/4</b>	20	80	197	17.63
8698-032	<b>32 d X 1</b>	15	90	197	23.46
8698-040	<b>40 d X 1-1/4</b>	10	0	197	44.59
8698-050	<b>50 d X 1-1/2</b>	10	0	197	55.46
8698-063	<b>63 d X 2</b>	5	0	197	85.35
8698-090	<b>90 d X 3</b>	5	0	197	201.43
8698-110	<b>110 d X 4</b>	4	0	197	231.28

### PVC Transition Union

**JIS (mm) Soc x ASTM (in.) Soc with Viton® O-ring Seal**




235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8257-016	<b>16 DN X 1/2</b>	20	160	197	10.46
8257-020	<b>20 DN X 3/4</b>	10	40	197	13.32
8257-025	<b>25 DN X 1</b>	15	90	197	15.20
8257-030	<b>30 DN X 1-1/4</b>	10	0	197	30.19
8257-040	<b>40 DN X 1-1/2</b>	10	0	197	34.19
8257-050	<b>50 DN X 2</b>	5	0	197	46.37
8257-075	<b>75 DN X 3</b>	5	0	197	86.31
8257-100	<b>100 DN X 4</b>	4	0	197	120.21

Part Number	Size	Std Pk	Mstr Ctn	Disc Code	Price Each
-------------	------	--------	----------	-----------	------------

### PVC Transition Union

**JIS (mm) Soc x ASTM (in.) Fipt with Viton® O-ring Seal**




235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8258-016	<b>16 DN X 1/2</b>	20	160	197	12.78
8258-020	<b>20 DN X 3/4</b>	20	80	197	17.86
8258-025	<b>25 DN X 1</b>	15	90	197	23.76
8258-030	<b>30 DN X 1-1/4</b>	10	0	197	45.37
8258-040	<b>40 DN X 1-1/2</b>	10	0	197	56.16
8258-050	<b>50 DN X 2</b>	5	0	197	86.41
8258-075	<b>75 DN X 3</b>	5	0	197	203.98
8258-100	<b>100 DN X 4</b>	4	0	197	234.43

### PVC Transition Union

**JIS (mm) Soc x ASTM (in.) Soc with EPDM O-ring Seal**




235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8297-016	<b>16 DN X 1/2</b>	20	160	197	10.33
8297-020	<b>20 DN X 3/4</b>	20	80	197	13.16
8297-025	<b>25 DN X 1</b>	15	90	197	15.05
8297-030	<b>30 DN X 1-1/4</b>	10	0	197	29.83
8297-040	<b>40 DN X 1-1/2</b>	10	0	197	33.77
8297-050	<b>50 DN X 2</b>	5	0	197	45.80
8297-075	<b>75 DN X 3</b>	5	0	197	85.23
8297-100	<b>100 DN X 4</b>	4	0	197	117.88

### PVC Transition Union

**JIS (mm) Soc x ASTM (in.) Fipt with EPDM O-ring Seal**




235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8298-016	<b>16 DN X 1/2</b>	20	160	197	12.60
8298-020	<b>20 DN X 3/4</b>	20	80	197	17.63
8298-025	<b>25 DN X 1</b>	15	90	197	23.46
8298-030	<b>30 DN X 1-1/4</b>	10	0	197	44.59
8298-040	<b>40 DN X 1-1/2</b>	10	0	197	55.46
8298-050	<b>50 DN X 2</b>	5	0	197	85.35
8298-075	<b>75 DN X 3</b>	5	0	197	201.43
8298-100	<b>100 DN X 4</b>	4	0	197	231.28

### PVC Transition Union

**BSP Thread (in.) x ASTM (in.) Soc with Viton® O-ring Seal**




235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8359-005	<b>1/2</b>	20	160	197	12.78
8359-007	<b>3/4</b>	20	80	197	17.86
8359-010	<b>1</b>	15	90	197	23.76
8359-012	<b>1-1/4</b>	10	0	197	45.37
8359-015	<b>1-1/2</b>	10	0	197	56.16
8359-020	<b>2</b>	5	0	197	86.41
8359-030	<b>3</b>	5	0	197	203.98
8359-040	<b>4</b>	4	0	197	234.43

### PVC Transition Union

**BSP Thread (in.) x ASTM (in.) Fipt with Viton® O-ring Seal**



235 psi Maximum Internal Pressure Rating @ 73°F (23°C)

8358-005	<b>1/2</b>	20	160	197	12.18
8358-007	<b>3/4</b>	20	80	197	17.01
8358-010	<b>1</b>	15	90	197	22.65
8358-012	<b>1-1/4</b>	10	0	197	43.21
8358-015	<b>1-1/2</b>	10	0	197	53.49
8358-020	<b>2</b>	5	0	197	82.31
8358-030	<b>3</b>	5	0	197	208.77
8358-040	<b>4</b>	4	0	197	245.35