

Part No: 828-120CF

Fabricated Fittings

Coupling

Desc: 12 CPVC REPAIR COUPLING GASKET SCH80

MSRP: 1524.73

Part Code: 097

Weight(lbs): 53.33

Weight(kg): 24.19

Weight(gm): 24190

Size: 12"

Color: GRAY

Material: CPVC

Schedule SCH 80

Connection Gasket X Gasket

Type Standard



L = 29

L1 = 21-3/8

M = 14- 1/8

M1 = 15-3/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ inch & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

