

Part No: 828-140CF

Fabricated Fittings

Coupling

Desc: 14 CPVC REPAIR COUPLING GASKET S80

MSRP: 4487.92

Part Code: 097

Weight(lbs): 68.674

Weight(kg): 31.15

Weight(gm): 31150

Size: 14"

Color: GRAY

Material: CPVC

Schedule SCH 80

Connection Gasket X Gasket

Type Standard



L = 30

L1 = 21

M = 15-1/2

M1 = 17-1/4

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ inch & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

