

Part No: 828-160CF

Fabricated Fittings

Coupling

Desc: 16 CPVC REPAIR COUP GASKET SCH80

MSRP: 6354.19

Part Code: 097

Weight(lbs): 71.172

Weight(kg): 32.283

Weight(gm): 32283

Size: 16"

Color: GRAY

Material: CPVC

Schedule SCH 80

Connection Gasket X Gasket

Type Standard



L = 31

L1 = 22-1/4

M = 17-11/16

M1 = 18-7/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.
- L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; ± 1/4 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.
- W** = Height of cap; ± 1/4 inch.

Typical Fabricated Dimension References

