

Part No: 829-528CFE

Fabricated Fittings

Coupling

Desc: 6X2 CPVC ECC RED COUP SOC SCH80

MSRP: 656.89

Part Code: 097

Weight(lbs): 5.401

Weight(kg): 2.45

Weight(gm): 2450

Size: 6"X2"


Color: GRAY

Material: CPVC

Schedule SCH 80

Connection Socket X Socket

Type Eccentric Reducer



L = 20- 7/8

M = 7- 5/16

M1 = 2-13/16

N = 15- 7/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ inch & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

