

Part No: 829-700F

Fabricated Fittings

Coupling

Desc: 14X10 PVC RED COUPLING SOC SCH80

MSRP: 1040.42

Part Code: 083

Weight(lbs): 24.712

Weight(kg): 11.209

Weight(gm): 11209

Size: 14"X10"


Color: GRAY

Material: PVC

Schedule SCH 80

Connection Socket X Socket

Type Reduction



L = 18- 1/8

M = 15- 3/16

M1 = 11-15/16

N = 5- 7/8

Fabricated Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.

H = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.

L = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.

M = Outside diameter of socket/thread hub; $\pm 1/4$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.

W = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

