

Part No: 829-790F

Fabricated Fittings

Coupling

Desc: 18X10 PVC RED COUPLING SOC SCH80

MSRP: 3452.03

Part Code: 083

Weight(lbs): 84.591

Weight(kg): 38.37

Weight(gm): 38370

Size: 18"X10"


Color: GRAY

Material: PVC

Schedule SCH 80

Connection Socket X Socket

Type Reduction



L = 35- 3/8

M = 19-11/16

M1 = 11-15/16

N = 21- 1/8

Fabricated Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/4$ & larger $\pm 1/2$ inch.
- H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; $\pm 1/4$ inch.; wyes $\pm 1/2$ inch; 14" & larger inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/4$ inch; 14" & larger $\pm 1/2$ inch.
- L** = Overall length of fittings; $\pm 1/2$ inch; wyes ± 1 inch; 14" & larger ± 1 inch.
- M** = Outside diameter of socket/thread hub; $\pm 1/4$ inch.
- N** = Socket bottom to socket bottom; couplings; $\pm 1/2$ inch.
- W** = Height of cap; $\pm 1/4$ inch.

Typical Fabricated Dimension References

