

Part No: 854-010CL300C

All

80C-1

Desc: 1 CPVC V/S FLANGE SOC CL300 150PSI FAB

MSRP: 564.76

Part Code: 097

Weight(lbs): 0.626

Weight(kg): 0.284

Weight(gm): 284

Size: 1

Color:

Material:

Connection Soc

Under

Development

L = 1- 1/4

M = 1- 3/4

N = 3/16

Max. = 4- 7/8
O.D.

R = 1

No of
Bolts = 4

Bolt
Circle = 3- 1/2
Dia.

Bolt Size = 5/8

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

