

Part No: 854-025CL300C

All

80C-1

Desc: 2-1/2 CPVC V/S FLANGE SOC 150 PSI CL300

MSRP: 823.51

Part Code: 097

Weight(lbs): 3.84

Weight(kg): 1.742

Weight(gm): 1742

Size: 2-1/2

Color:

Material:

Connection Soc

Under

Development

L = 2

M = 3- 9/16

N = 1/4

Max. = 7- 1/2
O.D.

R = 1

No of
Bolts = 8

Bolt
Circle = 5- 7/8
Dia.

Bolt Size = 3/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

