

Part No: 854-160CL300C

All

80C-1

Desc: 16 CPVC VAN STONE FLNGE SOC CL300 150PSI

MSRP: 5062.3

Part Code: 097

Weight(lbs): 44.789

Weight(kg): 20.316

Weight(gm): 20316

Size:

Color:

Material:

Connection Soc

Under

Development

L = 8- 9/16

M = 17- 3/4

N = 9/16

Max. = 25- 1/2
O.D.

R = 2

No of
Bolts = 20

Bolt
Circle = 22- 1/2
Dia.

Bolt Size = 1- 1/4

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

