

Part No: 859-020SR

Schedule 80 PVC & CPVC

Union

Desc: 2 PVC UNION SOCXSRFPT FKM

MSRP: 90.01

Part Code: 086

Weight(lbs): 1.131

Weight(kg): 0.513

Weight(gm): 513


Size: 2"

Color: GRAY

Material: PVC

Connection Socket x SR Fipt

O-Ring FKM



L = 4- 3/32

M = 3-1/16

N = 1-19/32

NUT = 4- 3/16
O.D.

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

L = Overall length of fittings; ± 1/16 inch.

M = Outside diameter of socket/thread hub; ± 1/16 inch.

N = Socket bottom to socket bottom; couplings; ± 1/16 inch.

W = Height of cap; ± 1/16 inch

Typical Molded Dimension References

